


1200 max




Δ longueur max de passage 800 mm

BALLON EG

	Unit	Value	Remarks
Max Zul Druck	[bar]	5	
Max allow pressure			
Min/Max Zul Température	[°C]	100	
Min/Max allow temperature			
Prüfdruck	[bar]	12	
Test pressure			
Volumen	[m³]	1705	✓
Capacity			
Oberflächenbearbeitung			Ø 100 x 100 x 100
Surface treatment			
Werkstoff			1.4571 / 1.4570
Material			
Gewicht		740	
Weight			
Artikel-Nr.			
Article number			

1200 max



Für die Lage der Stützen ist ausschließlich die Draufsicht verbindlich!

Nozzle direction only according to the top view!

Item	Description	Quantity	Material
1	Muffenschlüssel / Adapter connection	2/177	1.4571
2	Muffenschlüssel / Adapter connection	2/177	1.4571
3	Muffenschlüssel / Adapter connection	2/177	1.4571
4	Muffenschlüssel / Adapter connection	2/177	1.4571
5	Muffenschlüssel / Adapter connection	2/177	1.4571
6	Muffenschlüssel / Adapter connection	2/177	1.4571
7	Muffenschlüssel / Adapter connection	2/177	1.4571
8	Muffenschlüssel / Adapter connection	2/177	1.4571
9	Muffenschlüssel / Adapter connection	2/177	1.4571
10	Muffenschlüssel / Adapter connection	2/177	1.4571
11	Muffenschlüssel / Adapter connection	2/177	1.4571
12	Muffenschlüssel / Adapter connection	2/177	1.4571
13	Muffenschlüssel / Adapter connection	2/177	1.4571
14	Muffenschlüssel / Adapter connection	2/177	1.4571
15	Muffenschlüssel / Adapter connection	2/177	1.4571
16	Muffenschlüssel / Adapter connection	2/177	1.4571
17	Muffenschlüssel / Adapter connection	2/177	1.4571
18	Muffenschlüssel / Adapter connection	2/177	1.4571
19	Muffenschlüssel / Adapter connection	2/177	1.4571
20	Muffenschlüssel / Adapter connection	2/177	1.4571
21	Muffenschlüssel / Adapter connection	2/177	1.4571
22	Muffenschlüssel / Adapter connection	2/177	1.4571
23	Muffenschlüssel / Adapter connection	2/177	1.4571
24	Muffenschlüssel / Adapter connection	2/177	1.4571
25	Muffenschlüssel / Adapter connection	2/177	1.4571
26	Muffenschlüssel / Adapter connection	2/177	1.4571
27	Muffenschlüssel / Adapter connection	2/177	1.4571
28	Muffenschlüssel / Adapter connection	2/177	1.4571
29	Muffenschlüssel / Adapter connection	2/177	1.4571
30	Muffenschlüssel / Adapter connection	2/177	1.4571
31	Muffenschlüssel / Adapter connection	2/177	1.4571
32	Muffenschlüssel / Adapter connection	2/177	1.4571
33	Muffenschlüssel / Adapter connection	2/177	1.4571
34	Muffenschlüssel / Adapter connection	2/177	1.4571
35	Muffenschlüssel / Adapter connection	2/177	1.4571
36	Muffenschlüssel / Adapter connection	2/177	1.4571
37	Muffenschlüssel / Adapter connection	2/177	1.4571
38	Muffenschlüssel / Adapter connection	2/177	1.4571
39	Muffenschlüssel / Adapter connection	2/177	1.4571
40	Muffenschlüssel / Adapter connection	2/177	1.4571
41	Muffenschlüssel / Adapter connection	2/177	1.4571
42	Muffenschlüssel / Adapter connection	2/177	1.4571
43	Muffenschlüssel / Adapter connection	2/177	1.4571
44	Muffenschlüssel / Adapter connection	2/177	1.4571
45	Muffenschlüssel / Adapter connection	2/177	1.4571
46	Muffenschlüssel / Adapter connection	2/177	1.4571
47	Muffenschlüssel / Adapter connection	2/177	1.4571
48	Muffenschlüssel / Adapter connection	2/177	1.4571
49	Muffenschlüssel / Adapter connection	2/177	1.4571
50	Muffenschlüssel / Adapter connection	2/177	1.4571
51	Muffenschlüssel / Adapter connection	2/177	1.4571
52	Muffenschlüssel / Adapter connection	2/177	1.4571
53	Muffenschlüssel / Adapter connection	2/177	1.4571
54	Muffenschlüssel / Adapter connection	2/177	1.4571
55	Muffenschlüssel / Adapter connection	2/177	1.4571
56	Muffenschlüssel / Adapter connection	2/177	1.4571
57	Muffenschlüssel / Adapter connection	2/177	1.4571
58	Muffenschlüssel / Adapter connection	2/177	1.4571
59	Muffenschlüssel / Adapter connection	2/177	1.4571
60	Muffenschlüssel / Adapter connection	2/177	1.4571
61	Muffenschlüssel / Adapter connection	2/177	1.4571
62	Muffenschlüssel / Adapter connection	2/177	1.4571
63	Muffenschlüssel / Adapter connection	2/177	1.4571
64	Muffenschlüssel / Adapter connection	2/177	1.4571
65	Muffenschlüssel / Adapter connection	2/177	1.4571
66	Muffenschlüssel / Adapter connection	2/177	1.4571
67	Muffenschlüssel / Adapter connection	2/177	1.4571
68	Muffenschlüssel / Adapter connection	2/177	1.4571
69	Muffenschlüssel / Adapter connection	2/177	1.4571
70	Muffenschlüssel / Adapter connection	2/177	1.4571
71	Muffenschlüssel / Adapter connection	2/177	1.4571
72	Muffenschlüssel / Adapter connection	2/177	1.4571
73	Muffenschlüssel / Adapter connection	2/177	1.4571
74	Muffenschlüssel / Adapter connection	2/177	1.4571
75	Muffenschlüssel / Adapter connection	2/177	1.4571
76	Muffenschlüssel / Adapter connection	2/177	1.4571
77	Muffenschlüssel / Adapter connection	2/177	1.4571
78	Muffenschlüssel / Adapter connection	2/177	1.4571
79	Muffenschlüssel / Adapter connection	2/177	1.4571
80	Muffenschlüssel / Adapter connection	2/177	1.4571
81	Muffenschlüssel / Adapter connection	2/177	1.4571
82	Muffenschlüssel / Adapter connection	2/177	1.4571
83	Muffenschlüssel / Adapter connection	2/177	1.4571
84	Muffenschlüssel / Adapter connection	2/177	1.4571
85	Muffenschlüssel / Adapter connection	2/177	1.4571
86	Muffenschlüssel / Adapter connection	2/177	1.4571
87	Muffenschlüssel / Adapter connection	2/177	1.4571
88	Muffenschlüssel / Adapter connection	2/177	1.4571
89	Muffenschlüssel / Adapter connection	2/177	1.4571
90	Muffenschlüssel / Adapter connection	2/177	1.4571
91	Muffenschlüssel / Adapter connection	2/177	1.4571
92	Muffenschlüssel / Adapter connection	2/177	1.4571
93	Muffenschlüssel / Adapter connection	2/177	1.4571
94	Muffenschlüssel / Adapter connection	2/177	1.4571
95	Muffenschlüssel / Adapter connection	2/177	1.4571
96	Muffenschlüssel / Adapter connection	2/177	1.4571
97	Muffenschlüssel / Adapter connection	2/177	1.4571
98	Muffenschlüssel / Adapter connection	2/177	1.4571
99	Muffenschlüssel / Adapter connection	2/177	1.4571
100	Muffenschlüssel / Adapter connection	2/177	1.4571



Kippmaß/ Tilting height: 2250 mm